



PRODUCT INFORMATION SHEET

BJO-0930

PHENOSET MICROSPHERES

BJO-0930 hollow microspheres are reddish-brown in colour and primarily used as hollow filler. The density and maximum working pressure allow the formulator to choose the minimum density product that will survive the formulation, pumping and use.

TYPICAL PROPERTIES

Average Hydrostatic Compressive Strength	350 psi
Liquid Density (Liquid Displacement)	0.21 – 0.25 g/mL
Average Bulk Density	0.104 g/cc
Moisture Content	< 4 wt %
Mean Particle Size	90 microns by sieve method 65 microns by laser diffraction

PACKAGING

Polyethylene-lined cardboard boxes
Phenosest BJO-0930 : 12.0 kgs / 26.4 lbs

STORAGE AND HANDLING

- Store Phenosest microspheres in a cool, well-ventilated area
- Keep away from sunlight

For further information on storage and handling, please refer to the Material Safety Data Sheets.

PRODUCT SAFETY

When considering the use of MAC products in a particular application, kindly review our latest Material Safety Data Sheets and ensure that the use you intend can be accomplished safely. For Material Safety Data Sheets and other product safety information, contact Malayan Adhesives & Chemicals Sales / Distributor's Office nearest to you.

Date of issue :April 19, 2019

IMPORTANT : This information is not to be taken as a warranty or representation for which we assume legal responsibility nor as permission or recommendation to practice any patented invention without license. It is offered solely for your consideration and investigation. Since your specific application and conditions of use are beyond the control of Malayan Adhesives & Chemicals Sdn Bhd, you must determine the suitability of the products and the suggestions mentioned herewith for your specific application.